




# EASY FITTING

## THE EASIEST WAY TO CONNECT YOUR PUMP

Easy Fitting™ from QED lower the cost of disconnecting & reconnecting tubing when cleaning pumps.




### DO YOUR FIELD CREWS SPEND TOO MUCH TIME AND MONEY ON:

- Cutting tubing from the pump's barbed fittings during pump removal?
- Removing and replacing tubing clamps?
- Precision cutting the air, exhaust and liquid discharge tubing for proper alignment?

### EASY FITTING ADVANTAGES

- Highly corrosion-resistant stainless steel.
- Easily disassembled and reassembled.
- No need to cut the tubing shorter every time a pump is removed for cleaning.
- Faster
- No Clamp removal/replacement
- No need to cut the tubing shorter every time a pump is removed for cleaning

### How the Easy Fitting Works:



© Product designs and specifications are subject to change without notice. User is responsible for determining suitability of product.

**QED Environmental Systems Inc.**  
2355 Bishop Circle West Dexter, MI 48130, USA



**QED Environmental Systems Ltd.**  
Cyan Park, Unit 3 Jimmy Hill Way, Coventry CV2 4QP, UK

[info@qedenv.com](mailto:info@qedenv.com) 800.624.2026  
734.995.2547

[WWW.QEDENV.COM](http://WWW.QEDENV.COM)

[sales@qedenv.co.uk](mailto:sales@qedenv.co.uk) +44 (0) 333 800 0088

## THE TROUBLE WITH CONVENTIONAL BARBED FITTINGS

Pumps that are used in landfill gas wells and groundwater remediation wells periodically require removal for cleaning/maintenance. When the pumps are removed from the wells and disconnected from the hose/tubing, a significant amount of time is spent removing the clamp from the hose/tubing, and cutting the tubing away from the barbed fittings. Additionally, the cutting of the downwell tubing results in the tubing being shortened every time the pumps are removed from the well.

When reattaching the hose/tubing to the pumps, the three sections of hose/tubing (air supply, air exhaust and liquid discharge) must all be cut precisely to the staggered lengths needed to match the three barbed fittings on the pump.

## EASY FITTING ELIMINATES ALL THE HASSLES

With Easy Fittings, all three lines are easily disconnected by pulling the retaining clip out, and then simply pulling the hose/tubing away from the pump. After the pump cleaning/ maintenance is complete, the hose/tubing fitting is simply pushed into the pump fitting, and the retaining clip is reinserted to lock the fitting in place.

## ORDERING INFORMATION

### (FOR EXISTING PUMPS)

PART NO.	DESCRIPTION
303016	Easy Fittings Kit, 1" Discharge Tubing or 3/4" hose
303017	Easy Fittings Kit, 1-1/4" Discharge Tubing OR 1" hose

### (FOR NEW PUMPS)

PART NO.	DESCRIPTION
303012	Easy fittings Kit, 1 "Discharge Tube <b>OR</b> 3/4" hose
303013	Easy Fittings Kit, 1-1/4" Discharge Tubing <b>OR</b> 1" hose

## MATERIALS OF CONSTRUCTION:

### Fittings:

316 Stainless Steel

### Retaining clip:

Hastelloy C

### O-Rings:

Viton

### Maximum Pressure:

125 p.s.i.

